

Data sheet

DST2-QCAL-GB0 P2P3 / 26.7.2017 - V 2.4



Q caloric 5.5

Electronic device for heat cost allocation on the basis of measuring the share of heat output by radiators.

In terms of measuring technology, the Q caloric 5.5 is 100% compatible with the Q caloric 5. All assembly-related properties also match the Q caloric 5.

The Q caloric 5.5 has improved and extended wireless properties. Available as a compact and remote sensor variant.



Application

The Q caloric 5.5 is the successor model to the tried-and-trusted Q caloric 5. In addition to improved energy management, the Q caloric 5.5 can be operated in different wireless modes. In terms of measuring technology, the Q caloric 5.5 is 100% compatible to the Q caloric 5. Installation instructions can be taken over from the Q caloric 5 without changes being necessary. Communication with the current software versions of the Q suite 5 caloric (V2.1 or higher) and ACT46 (V1.6 or higher) is possible without restrictions.

In S mode (walk-by & AMR), the Q caloric 5.5 is 100% compatible to the Q caloric 5. In C-mode (walk-by & OMS) the wireless capacities and ranges have been significantly improved compared to the Q caloric 5 in S-mode.

The electronic heat cost allocator Q caloric 5.5 has been designed for decentralised use. Values are measured through one (radiator) or two (radiator and room air temperature) temperature sensors. In 2-sensor operation the actual difference in temperature between the ambient temperature and the radiator temperature is determined, in 1-sensor operation a constant value is prescribed for the ambient temperature.

These measured values are used as a basic for calculation of the consumption calculation. The main area of application is in central heating systems where the heating energy is used individually by different consumers. The electronic heat cost allocator can be operated as a 1-sensor measuring system or 2-sensor measuring system with product and unit scale.

Such systems are used in e.g.:

- Apartment buildings
- Offices and administration buildings

Typical users are:

- Meter reading service companies
- > Housing industry and housing associations
- > Building service companies and property management

The heat cost allocator can be used for the following types of radiator:

- Ribbed radiators
- Tubular radiators
- > Panel-type radiators with horizontal and vertical water flow
- > Radiators with internal tube register
- Convectors

AMR

The electronic heat cost allocators Q caloric 5.5 type P2 and P3 are equipped with the AMR radio transmitter of the WHE4x device family.

The rcu4 radio system is not supported by the Q caloric 5.5.

OMS

In C-mode the electronic heat cost allocator Q caloric 5.5 transmits OMS telegrams (OMS = Open Metering System) parallel to the walk-by telegrams. The OMS telegrams meet the "Open Metering System Specification" and can thus be received by all OMS-compatible devices.



Data interface

The electronic heat cost allocators Q caloric 5.5 type P2 and P3 can be equipped with the IrDA close-range interface of the device family WHE3x/WHE4x.

The 1107 data interface is not supported by the Q caloric 5.5.

Programming accessories

The programming accessories are used for communication with the metering devices.

Programming adapter:

The programming adapter can be used as an individual programming tool and as a combi-adapter with the IrDA programming and readout head.

IrDA programming and readout head(*):

The IrDA programming and readout heat is used as a communication tool between a PC/netbook and the meter. The meter can be programmed and read out using the Q suite 5 caloric (V2.1 or higher).

(*) Only necessary for meters without an integrated IrDA close-range interface.

Programming possibilities

The following information can be programmed before the measuring device is put into operation:

Standard parameters

- Sensor type
 - 1-sensor or 2-sensor measuring system
- K-value / KC / KQ
 Evaluation factors for calculating radiator heat output (depending on the meter algorithm and sensor type)
 Next due date
- Day the annual value is stored

(can also be programmed without IrDA interface using the programming adapter)


Device name / device code Device access data as protection from unauthorised device access



Displays

Device states, consumption values and measuring system information are displayed on the LCD in a display loop.

Display loops in normal operation:






Displays


The meters are delivered from the factory in sleep mode. Measuring operation is inactive.

Device display loops in sleep mode





Displays





Radio (wireless) features S-mode

- > Radio system parallel transmission of walk-by and AMR data telegrams
- Transmission delay (offset)
 Time delay for sending telegrams after the due date or at the beginning of the moth in days (standard = 0 days)
 Transmission-free day
- A maximum of 2 days from Friday, Saturday and Sunday can be defined as transmission-free days At least 1 day must be set (standard = Sunday).
- No change with the remote sensor system

Transmission behaviour	
walk-by(*)	AMR
every 128 seconds	every 4 hours
10 hours per day (8 am - 6 pm)	24 hours per day
monthly: 4 readout dates after the first day of each month	7 days per week
annual: 48 hours after due date	365 days per year
current consumption values 13 Statistic values	data telegrams or statistics and consumption values

(*) Compatible with Q caloric 5 / transmission delay or transmission-free days for walk-by only available in S-mode.

Radio (wireless) features C-mode

- > Radio system parallel transmission of walk-by and OMS data telegrams
- Increased radio capacity in C-mode (10 dBm)
- > No change with the remote sensor system

Transmission behaviour	
walk-by ⁽¹⁾	OMS ⁽²⁾
every 112 seconds	every 7.5 minutes
10 hours per day (8 am - 6 pm)	24 hours per day
365 days per year	365 days per year
current consumption values 13 Statistic values	current consumption values

⁽¹⁾ For this, you need the mobile data logger Q log 5.5 and the readout software ACT46.PC V1.6.

The readout software can be downloaded from http://qdc.qundis.com.

⁽²⁾ OMS "Open Metering System" communication architecture for intelligent meters for different manufacturers and branches.

Mode change

It is possible to change between S-mode and C-mode in both directions.

For this, you need the Q suite 5 caloric (V2.1 or higher), a programming adapter(*) or an IrDA programming and readout head.

(*) Programming adapter and IrDA programming and readout head necessary for meters without an integrated IrDA close-range interface.




Technical features

Device data	
	as 1-sensor measuring system - with dynamic heating operation detection
Measuring system	as 2-sensor measuring system - 1 sensor each for radiator and room air tempera-
	ture
Device type	Q caloric 5.5 (P2) profile compatibility HKVE 20x
	Q caloric 5.5 (P3) profile compatibility WHEx
Power supply	3V lithium battery
Service life	typ. 10 years
Display	Liquid crystal display (LCD)
Scope of display	5 digits (00000 99999)
	Algorithm 2: K-values
	1-sensor measuring system 255 values (basis: K-value 26)
Freebookies	2-sensor measuring system 999 values (basis: K-value 60)
Evaluation	
	Algorithm 3/4: Repair and extension installations
	Existing information in the system manual for the WHEx models
Radiator power range	21 Watt 9,999 Watt
Sensor temperature range	0 °C 105 °C
tm-max	105 °C (compact device), 105 °C (remote sensor device)
tm-min ^(*)	35 °C (2-sensor system), 55 °C (1-sensor system)
(*) mean design temperature	
Temperature sensor	NTC, prematurely aged
Device versions	Compact device
	Remote sensor device (compact device with inserted remote sensor)
	Remote sensor cable lengths: 1.5 m, 2.5 m and 5.0 m
	New installation and conversion:
	Q caloric 5.5 with existing installation material
lastellation material	
Installation material	Standard replacement, extension installation and repair replacement:
	Q caloric 5.5 with installation material following the families
	HKVE 20x and WHE3x/WHE4x

Norms and standards		
Heat cost allocator for acquir- ing consumption data for room heating	DIN EN 834:2013	
Type approval acc. to HKVO	A1.01.2011 - Q caloric 5.5 - P2 C3.01.2011 - Q caloric 5.5 - P3	
CE conformity	Directive 2014/30/EU (Electromagnetic Compatibility)	
	With radio support Directive 2014/53/EU (RED Directive)	



Dimensioning drawing of the device



Restrictions

Electronic heat cost allocators cannot be used with steam heaters, fresh-air radiators, underfloor heating, ceiling heating elements or flap-controlled radiators.

In the case of combined valve and flap-controlled radiators, metering devices may only be installed if the flap control unit has been removed or disabled in the "open" position.

Convectors that can change their output through an electric fan and towel heaters with an electric heating cartridge must not be fitted with electronic heat cost allocators unless the respective electric system has been removed or disabled. A joint use of different metering device types is only allowed within a property as long as they all use a standard metering system and have a standard measuring algorithm.

Compatibility


The 202R can NOT be replaced by the Q caloric 5.5 AMR since the radio transmitter fitted in the heat cost allocator is not compatible with the rcu4 system.

Equally, the WHE2 can NOT be replaced by the Q caloric 5.5, since both the measuring algorithm and the radio transmitter fitted in the heat cost allocator (with WHE26) are not compatible.

1-sensor and 2-sensor metering system



Dimensioning drawing of the snap-on panel



🖂 QUNDIS GmbH

©2017 QUNDIS GmbH. Subject to change